CENTRAL SERICULTURAL GERMPLASM RESOURCE CENTRE CENTRAL SILK BOARD, P.B. NO.44 THALLY ROAD HOSUR-635 109, KRISHNAGIRI DIST., TAMILNADU

Phone: 04344-221148 FAX: 04344-220520

Grams: GERMPLASM

No.CSB/GRC/SE/LUMINAR AIR FLOW CHAMBER/09/Admn 589, 605 Date: 7:0

To:

UNDER CERTIFICATE OF POSTING

Sir,

1

Sub: - Inviting competitive quotations for supply of 1 No LAMINAR AIR FLOW CHAMBER (VERTICAL) - reg. ****

This office is interested in purchase of 1 No Laminar Air Flow Chamber specification enclosed. with The firms/suppliers/Manufacturers/dealers may offer their lowest rate for the same. They should also indicate the discount to be allowed on quoted value for the said branded item and clearly indicate the Tax/Transportation charge if any with the manufacturer Catelogue, Users List and performance report from the users, Warranty, Authorisation & Validity certificate from the manufacturer if not manufacturer.

Quotations should be addressed to the Director, Central Sericultural Germplasm Resources Centre, P.B. No. 44, Thally Road, Hosur-635 109, Tamilnadu and sent in a sealed envelope superscribing Krishnagiri Dist, "QUOTATION FOR SUPPLY OF LAMINAR AIR FLOW CHAMBER (VERTICAL)" The quotations should reach this office on or before 1.7.2010 at 15:00 hours. The quotations received after the due date and Time of receipt will be rejected summarily. Opening of quotation: 15.30 hours of 1.7.2010.

The Director reserves the right to accept or reject any or all quotations without assigning any reason whatsoever.

P.T.O

Contnd..... P-2

TERMS AND CONDITIONS

(1) EMD Quantum: Rs.2,000/-

Form: Demand Draft, Bank Guarantee favouring Director, Central Sericultural Germplasm Resources Centre, Hosur, payable at Hosur Branch. No interest will be paid.

- (2) Validity: Rate quoted should be valid for 90 Days.
- (3) Delivery Schedule: Should be within 10 days, after receipt of supply order.
- (4) Rate per unit should be quoted such as per piece in Indian Rupee only and delivery at CSGRC, Hosur- 635 109 (TAMILNADU). Guarantee/Warranty clause to be indicated.
- (5) Payment Schedule: By Demand Draft or Cheque after receipt of the stores in good working condition and confirming to specification.
- (6) Taxes/VAT/other statutory duties should be indicated separately. Please note that no form "C" or "D" will be issued by this station.
- (7) Liquidated damages for delay & non supply: 0.5% will be deducted from the bill per week for not supplying the work within the stipulated time.

(8) Submission of income tax clearance as issued by Income Tax Department & sales Tax clearance certificate as issued by State/Central Sales Tax Department. This office enjoys the benefit from payment of excise duty and is having valid DSIR certificate.

DIRECTOR

Mr. Car

0/0

Specifications for Laminar air flow chamber

Working Size	3 X 2 X 2 feet
Model	Vertical, entire unit to be made up of SS
	304 -316 grade
Cleanness level	Class 100
Particle retention	0.3 μ and above
Velocity	90 FPM ± 20
Illumination	750-800 lumen
Noise level	60-65 decibels
HEPA filters	Micro clean glass fiber paper of
	international standard MINIPLEAT HEPA
	filters with fine corrugated aluminum foil
	separators, efficiency-99.97 %. Necessary
	tests like laser particle count to conform the
	cleanliness, DOP integrity test certification
i) :	and velocity profile and Differential
****	pressure measurement to confirm the
•	HEPA filters condition to be provided
	before dispatch
Pressure drop	23 mm WG
Pre filters	High efficient washable, Synthetic non
	woven polyester fabric with HDPE meshes
	reinforcement on both sides. Both filters
	are to be protected by grill arrangement,
Blower assembly	Particle retension-10-15 micron
Blower assembly THIII.	Spring suspended DIDW blower assembly
	for high performance at low sound level,
	single phase, 1440 rpm, Double shaft
	motor directly coupled with pair of
	centrifugal type aluminum impeller and
	enclosed within a specially designed MS
Workable table	Stainless steel with overed from for
" olimoio moio	Stainless steel with curved front for convenient working, Fluorescent lamp,
	UV lamps 254 nm-Phillip-Holland make,
	Clear acrylic UV resistant front doors,
	pressure manometer, to be fitted with a
	glass bead sterilizer and provision for LPG
	gas inlet connection, Additional exhaust
	system with perforated SS table
Standard accessories	Power point, caster wheels, illumination
	side screen etc
Power supply	220 V single phase, 50 Hz